


Product Features



- VGR-18 series and VLR-18 large flow pressure regulator is adopted
- Each high pressure interface is controlled by a separate globe valve for easy operation
- Filter is equipped
- Alarm can be optional to monitor gas usage
- Co2 Type Manifolds equipped with heater
- Inlet pressure Max. : 15MPa,
Outlet pressure Max. : 0.86MPa
Low temperature cylinder Inlet pressure: 3.5MPa



Typical Applications

- Mainly used for industrial, medical and other occasions requiring centralized gas supply
- This type of manifolds provides continuous gas supply
- This type of manifolds is a gas supply system, of which the gas supply cylinder is connected to two side, Low temperature cylinder as the main gas supply, high pressure cylinder as a backup.

Flow Chart



Ordering Information

V6M - G - G - L - 2 - W

Inlet Pressure Gauge

G: Pressure gauge
K: Contact gauge

Outlet Pressure Gauge

G: Pressure gauge
K: Contact gauge

Installation

W: Wall install
S: Stent install

cylinder number

1: one cylinder 3: three cylinder
2: two cylinder N: N the cylinder

cylinder position

L: Left side
R: Right side

